Cam follower without axial guide

Without interior ring


IKO RNAST

- **For shaft diameters from 7mm to 60mm**
- **With external cylindrical cage**
- With wiper seals
- Material: steel
- Working temperature: -20°C to +120°C




Assembly

- Use with rails with a minimum hardness of 40 HRC
- Tolerance of shaft: g6, h6
- Shaft hardness: 58-64 HRC, Ra 0.2



Typical application



DISCOUNTS

Qty.	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

Part number	Shaft Ø	ØD	C	Static load Co (N)	Dynamic load C (N)	Weight (g)	Stock*	Price each 1 to 5
RNAST-5	07	16	07,8	2390	2710	8,9	✔	14,50 €
RNAST-6	10	19	09,8	4550	4160	13,9	✔	15,72 €
RNAST-8	12	24	09,8	5890	5650	23,5	✔	16,38 €
RNAST-10	14	30	11,8	9680	9790	42,5	✔	16,99 €
RNAST-12	16	32	11,8	10900	10500	49,5	✔	18,04 €
RNAST-15	20	35	11,8	14300	12400	50,0	✔	18,85 €
RNAST-17	22	40	15,8	20900	17600	90,0	-	18,76 €
RNAST-20	25	47	15,8	24500	19400	135,0	✔	20,73 €
RNAST-25	30	52	15,8	28400	20800	152,0	-	23,29 €
RNAST-30	38	62	19,8	45400	30500	255,0	-	26,07 €
RNAST-35	42	72	19,8	50600	32400	375,0	-	28,75 €
RNAST-40	50	80	19,8	61100	35900	420,0	-	33,89 €
RNAST-45	55	85	19,8	66400	37400	460,0	-	34,77 €
RNAST-50	60	90	19,8	71700	38900	500,0	-	38,78 €

*Depending on avaibility - Dimensions in mm

Altri prodotti...



PRF_BM

Elementi di ancoraggio, Fissaggio centrale per piede



CHB

Riduttore a ruota e vite senza fine, fino a 22 Nm



BOX-TOR-G

Valigetta di guarnizioni toriche in nitrile, 3.00 x 1.50mm a 30.20 x...




DB

Ingranaggio conico - Acciaio 60C40, 2:1



NCT

Giunto di collegamento, Ad angolo fisso



LAT1

Attuatore lineare a motore, 1 ampere



BABpss

Perno autobloccante, Inox



HG5-ECO

Ingranaggio dritto acciaio - serie ECO, Acciaio C45



ZY

Piedino antivibrante cilindrico, Inox



BAGSS

Anello di bloccaggio inox, Inox



T5-16ECO

Puleggia dentata di posizionamento tipo T, Serie economica -



PTA100ssEB

Piede snodato con base stampata Ø100, 15000N

Prodotti correlati



NAST

Rotelle, Con anello interno



CF

Perno folle, Standard - acciaio