

# Double row **radial** contact ball bearings **New**

## Q4

## Steel

- Double row bearings are capable of handling axial loads in both directions as well as radial loads as they have a deep gorge and can accept movement between the balls and raceway.

- Static and dynamic loads are radial loads

- Materials:

Steel rings and balls


Polyamide cage

Double row of bearings



### Advantage

- For the same external diameter and bore, a bearing with two rows of balls is capable of handling higher loads than bearings with a single row of balls.



### DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-30%	On request

Part number	Ød	ØD1	B	Load (kN)		Speed (rpm)		Weight (kg)	Price each 1 to 5
				Dynamic (C)	Static (Co)	Grease	Oil		
Q4200-ATN9	10	30	14	9,05	5,10	16830	19800	0,049	6,46 €
Q4201-ATN9	12	32	14	10,39	6,08	15300	18000	0,053	6,64 €
Q4202-ATN9	15	35	14	11,66	7,35	13005	15300	0,059	7,21 €
Q4203-ATN9	17	40	16	14,50	9,31	11475	13500	0,090	8,47 €
Q4204-ATN9	20	47	18	17,44	12,25	9945	11700	0,140	9,49 €
Q4205-ATN9	25	52	18	18,62	14,31	8415	9900	0,160	9,90 €
Q4206-ATN9	30	62	20	25,48	20,38	7268	8550	0,260	12,47 €
Q4207-ATN9	35	72	23	34,40	27,93	6120	7200	0,400	17,39 €
Q4208-ATN9	40	80	23	36,36	31,85	5355	6300	0,500	23,66 €
Q4210-ATN9	50	90	23	40,18	39,20	4590	5400	0,580	31,79 €
Q4211-ATN9	55	100	25	44,00	43,12	4284	5040	0,800	41,20 €
Q4212-ATN9	60	110	28	56,06	53,90	4055	4770	1,100	52,99 €
Q4213-ATN9	65	120	31	66,25	65,66	3672	4320	1,450	68,75 €
Q4214-ATN9	70	125	31	68,80	72,03	3290	3870	1,500	72,05 €

Dimensions in mm

## Altri prodotti...



PR881

Ruota di rinvio, Serie 881



ESCON

Variatore di velocità 5A, 5 A



UCF

Cuscinetto a flangia quadrata in ghisa, Ghisa



CHML50

Riduttore a ruota e vite senza fine, fino a 107 Nm - Con limitatore ...



PSG08

Ingranaggio dritto di precisione, Acciaio 35NCD6 pretrattato



BSM

Pressore a molla con esagono incassato, corpo in acciaio, spina in p...



PRF\_ART

Cerniere e giunti, Standard



BS2

Panamech, Multi-Beam, Alluminio - con vite a pressione



PM2

Coppia ruota e vite senza fine, Bronzo



UGH20

Unità di guida tipo H, Per martinetti Ø20



GLT3E-58

Guide telescopiche acciaio, Estensione extra



AT5courroie

Cinghia chiusa posizionamento AT, AT5 Poliuretano armatura in acciaio

## Prodotti correlati




Q1

Cuscinetto orientabile a sfere, Acciaio



QTR

Cuscinetto a rulli conici, Acciaio



KM

Cuscinetti a sfere - Accessorio, Ghiera KM



EAR

Cuscinetti a sfere - Accessorio, Ghiera autobloccante - anello di fr...