

Sealing strip **FDA approved**

RJABLU

Silicone

Silicone edge protection profiles with integrated steel retaining strip FDA approved

- Material :

VMQ (silicone rubber), hardness 60°

+/-5 Shore A, FDA approved.

Clamping insert stainless steel 304

- Colour: blue similare to RAL5015

- Operating T°: -50°C to +200°C

Assembly


- Easy, quick and smooth assembly. The edge protection profile is easy to push on by hand, and remains in place even on radii or bends. No adhesive or fastening material required

Uses


- Due to the use of FDA-compliant materials with approval according to FDA 21 CFR 177.2600 can be utilise in applications with corresponding requirements, including in the food industry

Info


- Supplied by the roll




Form A :



Form B :



Minimum bend radius



DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-5%	On request

Part Number	Form	Length (mm)			Clamping range (mm)	Minimum bend radius				Price each
						A	B	C	D	
RJA810-BLU/2	A	2000	8	10	1,0-2,0	10	20	10	10	
RJA810-BLU/5	A	5000	8	10	1,0-2,0	10	20	10	10	
RJA810-BLU/10	A	10000	8	10	1,0-2,0	10	20	10	10	
RJA810-BLU/20	A	20000	8	10	1,0-2,0	10	20	10	10	
RJA810-BLU/50	A	50000	8	10	1,0-2,0	10	20	10	10	
RJA1014-BLU/2	B	2000	10	14,5	3,0-4,0	45	120	30	30	
RJA1014-BLU/5	B	5000	10	14,5	3,0-4,0	45	120	30	30	
RJA1014-BLU/10	B	10000	10	14,5	3,0-4,0	45	120	30	30	
RJA1014-BLU/20	B	20000	10	14,5	3,0-4,0	45	120	30	30	
RJA1014-BLU/50	B	50000	10	14,5	3,0-4,0	45	120	30	30	

Dimensions in mm

Sealing strip FDA approved

Silicone

RJABLU

Silicone edge protection profiles with integrated steel retaining strip FDA approved

- Material :
VMQ (silicone rubber), hardness 60°
+/-5 Shore A, FDA approved.
Clamping insert stainless steel 304
- Colour: blue similare to RAL5015
- Operating T°: -50°C to +200°C

Assembly

- Easy, quick and smooth assembly. The edge protection profile is easy to push on by hand, and remains in place even on radii or bends. No adhesive or fastening material required

Uses

- Due to the use of FDA-compliant materials with approval according to FDA 21 CFR 177.2600 can be utilise in applications with corresponding requirements, including in the food industry

Recommendation



The sealing is recommended to be compressed to a maximum of 50% (compression) when using edge protection profiles.

To ensure the best possible sealing, the seal should be compressed by about 30-40%.


The information provided a recommendation only and may vary in practical cases depending on the application and parts used

Info

- Supplied by the roll



Minimum bend radius



DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-5%	On request

Part Number	Form	Length (mm)	Clamping					Minimum bend radius				Price each
			B	B1	H	H1	range (mm)	A	B	C	D	
RJA1121-BLU/2	A	2000	11,5	-	21	10,1	1,5-3,5	200	150	30	30	
RJA1121-BLU/5	A	5000	11,5	-	21	10,1	1,5-3,5	200	150	30	30	
RJA1121-BLU/10	A	10000	11,5	-	21	10,1	1,5-3,5	200	150	30	30	
RJA1121-BLU/20	A	20000	11,5	-	21	10,1	1,5-3,5	200	150	30	30	
RJA1121-BLU/50	A	50000	11,5	-	21	10,1	1,5-3,5	200	150	30	30	
RJA913-BLU/2	B	2000	8,8	11,1	13,1	-	1,0-3,0	50	40	80	100	
RJA913-BLU/5	B	5000	8,8	11,1	13,1	-	1,0-3,0	50	40	80	100	
RJA913-BLU/10	B	10000	8,8	11,1	13,1	-	1,0-3,0	50	40	80	100	
RJA913-BLU/20	B	20000	8,8	11,1	13,1	-	1,0-3,0	50	40	80	100	
RJA913-BLU/50	B	50000	8,8	11,1	13,1	-	1,0-3,0	50	40	80	100	

Dimensions in mm