

# Toggle clamps

## Rapid clamping - reliable fastening

**Durable and reliable:** More reliable, more user-friendly and safer. These clamps are quick to use, reliable and accurate. The use of high quality materials ensures a long working life.


### Advantages

- **Extremely tough** : All models will withstand 300,000 clamping cycles without problems
- **Durable** : High-quality bushes - no scratching
- **Extremely robust** : tCorrosion-resistant NITROX coating
- **Easy to use** : The fixed headed nut facilitates spindle adjustment
- **Reliable** : Constant level of force during both opening and closing
- **Ideal where space is restricted** : The slim design allows sufficient space for safe operation
- **Robust by design** : Thanks to use of U-shaped conical clamping arm
- **Safe to use** : No sharp edges prevent risk of anything getting trapped
- **Quick to put into operation** : Can be easily modified thanks to a wide range of accessories
- **Ergonomic design** : Easy to operate whilst wearing work gloves
- **Reflection free finish** : Suitable for use around lasers
- **Risk free use** : With increased space between clamping arm and handle avoids risks of squashing
- **Extremely adaptable** : Rectangular mounting holes allows installation on existing fixing points
- **Efficient clamping and locking** : The integrated design avoids any risks of squashing. Easy to use even whilst wearing gloves.

### Locking mechanism – principal of operation



1. Locked in closed position. Redesigned handle ensures safe operation as the smooth contours avoid any risk of anything being trapped.



2. Inner locking mechanism with automatic safety catch. The lock is released by pulling the handle.



3. Locked in open position. Releasing the handle engages the locking mechanism.



# Vertical toggle clamp

New

## SLVHLOK

## With locking mechanism

**High quality swivel bush with vertical foot and adjustable spindle**

Constant level of force during both opening and closing


Increased stability thanks to U-shaped clamping arm Fitted with automatic locking mechanism

- Material :



Nitro carburised steel with blackened finish

Polyamide handle


Locking mechanism TPE



**Hole positions**  
SLVH-6/LOK - SLVH-8/LOK



**Hole positions**



### DISCOUNTS

Qty	1+	6+	15+	20+
Disc.	List	-5%	-10%	On request

Part number	Opening angle (holding arm)			Opening angle (Handle)			Manual force N	Holding force		Clamping force	
	Pos. 1	Pos. 2	Stop pin removed	Pos. 1	Pos. 2	Stop pin removed		F1 (N)	F2 (N)	F3 (N)	F4 (N)
SLVH-6/LOK	56°	83°	156°	46°	56°	84°	160	1350	1650	920	1050
SLVH-8/LOK	13°	93°	157°	26°	61°	86°	190	2000	2800	940	1350
SLVH-10/LOK	6°	97°	175°	19°	59°	91°	250	2500	4500	1500	2800
SLVH-12/LOK	11°	88°	163°	24°	60°	91°	280	3000	5500	1400	2800

Part number	M	A	A1	A2	A3	B	B1	B2	B3	B4	B6	C	ØD	H	L	L1	Price
																	each 1 to 5
SLVH-6/LOK	M6x35	14	29	7	12	27	38	17,5	12,4	-	53,4	24,7	5,5	162,9	86,5	53	49,82 €
SLVH-8/LOK	M8x45	21	39	9	19	32	45	20,6	15,5	-	51,1	32,7	6,8	191,4	107	62	51,99 €
SLVH-10/LOK	M10x55	32	50	8	27	45	64	25,5	18,4	38	56,5	38,7	9	230,5	153	95	71,20 €
SLVH-12/LOK	M12x70	32	53	10,5	-	45	63	28	20,9	-	56,5	46,7	8,8	249,1	173,5	113,5	73,59 €

## Altri prodotti...




HTD5M\_09  
Puleggia dentata di trasmissione tipo HTD, HTD5 Alluminio




VPPTss  
Volantino pieno con impugnatura girevole, Inox 304



P20  
Riduttore a ruota e vite senza fine, fino a 5 Nm



CAB  
Cavo di fissaggio, Acciaio galvanizzato



VKM  
Dado quadrato in acciaio, Acciaio - 1 filetto



CHAR7520  
Cerniera a molla, avvitabile



OPFL\_OPPM  
Accessorio per indicatori, Pomello di manovra



Q3  
Cuscinetto a doppia corona di sfere, Obliquo - Acciaio



DOMI120  
Slitta di regolazione Domino 120, Slitta DOMILINE 120



PW\_PWG3  
Vite senza fine di precisione, Inox



Q4  
Cuscinetto a doppia corona di sfere, Radiale - Acciaio



PRF\_PA  
Elementi di giunzione, Piastra di adattamento

## Prodotti correlati



SLH-M  
Dado per bloccaggio a leva, Dado con estremità sferica



SLV  
Attrezzo di bloccaggio a leva verticale, A leva verticale - inox