



Support rod for heavy loads


Max load 90,000 N

TCL

- Threaded levelling stem, suitable for heavy loads
- Hollowed stem
- Fine pitch thread allows accurate levelling
- Material:
Chromed steel

Applications

- Machine tools, assembly machines, automated lines



DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØD	ØD1	SW	ØF	H	Static	Price each
						load (N)	1 to 5
TCL-M30C-110	M30x2	27	24	17	110	70000	18,92 €
TCL-M36C-110	M36x2	33	27	17	110	90000	20,71 €

Dimensions in mm

Adjusting nut


Fine thread

ECL

- Adjusting nut
- Fine thread
- Fine pitch thread allows accurate levelling
- Material:
Chromed steel

Applications

- Machine tools, assembly machines, automated lines




DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØD	SW	H	Price each
				1 to 5
ECL-M24C	M24x2	36	18	2,16 €
ECL-M27C	M27x2	41	12	4,07 €
ECL-M30C	M30x2	36	11	5,58 €
ECL-M35C	M35x2	55	15	8,92 €
ECL-M36C	M36x2	55	15	8,92 €
ECL-M36C3	M36x3	55	15	8,92 €
ECL-M42C	M42x2	65	20	16,16 €

Dimensions in mm

Altri prodotti...



PO

Maniglia a ponte -
Multi-settore, Foro
liscio



PAM_SS

Piede snodato con
base lamiera, Ø 30 &
40



SRG

Chiusura a leva
regolabile, Corsa da
96mm a 121,7mm



BVR

Battute a vite
regolabile, Acciaio



DCG

Ventosa, Gomma
naturale



GTC

Rullo tendicinghia, Per
applicazioni correnti



PCLA_M

Maniglia a ripresa -
femmina, Plastica



LRM

Dado cilindrico in
bronzo, Bronzo - 1
filetto



FIRSTDC1Q60

Variatore di velocità
10A, 10 A



NTMdl

Grano punta in delrin,
punta in delrin



ACLEPP

Angolare, 4 fori



G3

Ingranaggio dritto
acciaio, Acciaio
20NCD2

Prodotti correlati



TCL-ECL

Piede massiccio per
carichi pesanti, Dado
di regolazione



PML

Piede massiccio per
carichi pesanti, Ø 100,
120 o 150