

TC1RP

With 180° guide

- Tensioner for single chain

- Materials:

Housing: steel with corrosion proof epoxy finish



Profile: Green HD1000 polyethylene

Machine column: Black HD500 polyethylene



Screws and springs: stainless steel 304L

Adjustment

- Tension pressure can be reduced by freeing the springs, see instruction sheet



Detail A
Pre-tensioning spring



DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-10%	On request


Part number	Chain	A	C	Stroke	Tension (N)			Price each
					1 spring	2 springs	3 springs	
TC1-RP-06B1	06B1	5	30	40	60 to 132	120 to 264	180 to 396	211,11 €
TC1-RP-08B1	08B1	7	30	40	60 to 132	120 to 264	180 to 396	211,11 €
TC1-RP-10B1	10B1	9	30	40	60 to 132	120 to 264	180 to 396	211,11 €
TC1-RP-12B1	12B1	11	30	40	60 to 132	120 to 264	180 to 396	211,11 €

Dimensions in mm

Altri prodotti...



PR820
Ruota di rinvio, Serie 820 e 815



B
Ingranaggio conico - Acciaio 60C40, 1:1



ABL100005
Spazzola antistatica, Standard



OP2
Indicatore di posizione digitale (N. di giri), 3 cifre



NCT
Giunto di collegamento, Ad angolo fisso



MBrondele
Cuscinetti a sfere - Accessorio, Rondella di arresto MB



MEF
Cuscinetto cilindrico, Lega di ferro FP20 autolubrificante METAFRAM




SUA4_L
Giunzione per catena al metro, Falsa maglia - acciaio



LVT
Mini martinetto motorizzato 2A, 2



UCF_PBT
Cuscinetto a flangia quadrata polimero




T5M_T10M
Cinghia aperta al metro tipo T, T5




BTC
Tappo per tubo quadrato, Standard

Prodotti correlati



SUA4
Catena semplice al metro, Acciaio



SBS_M
Catena semplice al metro, Inox



TCXR
Tenditore per catena automatico, Con pignone acciaio



RLR
Tenditore per catena Roll-Ring®, Roll-Ring® Self-adjusting