


Linear guide system Drylin® W

WJRM



Hybrid bearings

- Drylin W hybrid bearings offer a unique combination of sliding and rolling movement. Depending on the mounting arrangement used, the use of maintenance free rollers reduce the driving force required. Any shear forces or shock forces are absorbed by the bearing. This hybrid bearing is ideally suited for manual adjustments especially in the applications such as door adjustments.
- Low driving force required, coefficient of friction 0.04 to 0.05 μ
- Highly cost effective solution
- Can be used with any of 7 profiles rails such as WS10, WS16 and WS20



Application

- Adjustable doors, machine guards, simple handling systems, furniture



New

Linear guide system Drylin® W


Sizes 10-16-20

WJRM

- **Material :**
Zamack
Liner manufactured from iglidur J

Advantages

- No lubrication required
- Small size
- Lightweight

NEW!**DISCOUNTS**

Qty	1+	6+	20+
Disc	Pri. -10%	On request	

Part number	Static load (W)	Dynamic load capacity for a total travel distance of (km)			F _{xv} Max (N.m/s)
		10 (N)	100 (N)	200 (N)	
WJRM01-10	250	250	90	50	50
WJRM01-16	400	400	140	70	80
WJRM01-20	550	550	200	100	80

Part number	A1	A3	B	B2	C1	C3	G1	H	K2	K3	Q1	Q2	Weight (g)	Price each 1 to 5
WJRM01-10	16,5	6,5	26	2,5	35	22	27	18	M6	M5	-	-	46	19,99 €
WJRM01-16	25	9	34,5	5	48	30	33	27	M8	M6	32	28	131	43,67 €
WJRM01-20	30	9	42,5	6	52	34	38	36	M8	M6	37	37	232	50,98 €

Dimensions in mm

Altri prodotti...



RBNtc

Ruota girevole a foro centrale, Acciaio - caucciù - a doppio blocca...



LRM

Dado cilindrico in bronzo, Bronzo - 1 filetto



VPR

Vite ad alette Hygienic Usit®, Inox



ABL100000

Spazzola antistatica, Per superfici fragili



ACLCHARJ

Cerniera ad avvitare, Adjusts in 2 directions



VELM6

Supporto avvitabile per rotolo a strappo fermacavi, Poliammide



SC2

Giunto rigido in 2 parti, Ganascia di serraggio



AT5M AT10M

Cinghia aperta al metro tipo AT, AT10 Poliuretano armatura in acciaio



CHAE3030PA

Cerniera ad avvitare estetica quadrata, Poliammide



SH0

Ingranaggio elicoidale ad assi paralleli, Acciaio 20NCD2



P70

Riduttore a ruota e vite senza fine, fino a 164 Nm



CHMR90

Riduttore a ruota e vite senza fine, fino a 540 Nm

Prodotti correlati



WS10

Guida modulabile Drylin® W, Binario



WS16

Binario Drylin® W, Binario



WS20

Binario Drylin® W, Binario