

Spur gear **with clamp**

Module
0,5

Teeth in polyacetal



- Spur gear are attached to the shaft by a friction coupling
- Precision grade JIS grade N10 (JIS B1702-1: 1998)
- Material:
Teeth polyacetal
Hub Stainless steel 303

Assembly



- Recommended shaft tolerances: g6, h6 or h7
- Torque slippage should be considered when making a selection

Info

- *Torque(bending strength)

NEW !

with clamping jaws



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØB Boss	ØA Bore	E	L	ØM screw	J	K	Torque* (Nm)	Slipping torque (Nm)	Mass (kg)	Price each
ZG0.5-36/SC	36	18	19	14	5	5	13,5	M2,5	3,3	4,4	0,49	0,62	0,012	
ZG0.5-40/SC	40	20	21	14	5	5	13,5	M2,5	3,3	4,4	0,55	0,62	0,012	
ZG0.5-50/SC	50	25	26	14	5	5	13,5	M2,5	3,3	4,4	0,73	0,62	0,013	
ZG0.5-60/SC	60	30	31	14	5	5	13,5	M2,5	3,3	4,4	0,90	0,62	0,015	
ZG0.5-80/SC	80	40	41	19	8	5	15	M3	4,5	6,0	1,25	2,22	0,019	
ZG0.5-120/SC	120	60	61	19	8	5	15	M3	4,5	6,0	1,93	2,22	0,040	

Dimensions in mm

Altri prodotti...



FF50

Riduttore ad alberi paralleli, da 111 a 425 Nm



SSB

Ingranaggio conico inox, 1:1



DOG316

Motoriduttore DC 12V e 24V DC, da 1.5 a 2 Nm



BSPM

Vite a ricircolo di sfere miniatura, Dado + vite a ricircolo di sfere



FDSQ

Flexible drive shaft, Masterflex® Steel, with PVC casing



SH0

Ingranaggio elicoidale ad assi paralleli, Acciaio 20NCD2



PSG255

Ingranaggio dritto di precisione, Inox 303



T5M T10M

Cinghia aperta al metro tipo T, T5 Poliuretano armatura in acciaio



BPLF

Sfera portante alta sporgenza, Leggero



SH0

Ingranaggio elicoidale ad assi paralleli, Plastica lavorata



PRF_ECL

Fissaggio, Dado quadrato con linguetta - Acciaio



DER90

Motore inox AC asincrono da 1,1 a 1,5kW, 1.1 a 1.5kW

Prodotti correlati