


# Linear guide system Drylin® W

## WJRM



## Hybrid bearings

- Drylin W hybrid bearings offer a unique combination of sliding and rolling movement. Depending on the mounting arrangement used, the use of maintenance free rollers reduce the driving force required. Any shear forces or shock forces are absorbed by the bearing. This hybrid bearing is ideally suited for manual adjustments especially in the applications such as door adjustments.
- Low driving force required, coefficient of friction 0.04 to 0.05 $\mu$
- Highly cost effective solution
- Can be used with any of 7 profiles rails such as WS10, WS16 and WS20



### Application

- Adjustable doors, machine guards, simple handling systems, furniture



**New**

# Linear guide system Drylin® W


Sizes 10-16-20

**WJRM**

- **Material :**  
Zamack  
Liner manufactured from iglidur J

**Advantages**

- No lubrication required
- Small size
- Lightweight

**NEW!****DISCOUNTS**

Qty	1+	6+	20+
Disc	Pri. -10%	On request	

Part number	Static load (W)	Dynamic load capacity for a total travel distance of (km)			F <sub>xv</sub> Max (N.m/s)
		10 (N)	100 (N)	200 (N)	
WJRM01-10	250	250	90	50	50
WJRM01-16	400	400	140	70	80
WJRM01-20	550	550	200	100	80

Part number	A1	A3	B	B2	C1	C3	G1	H	K2	K3	Q1	Q2	Weight (g)	Price each 1 to 5
WJRM01-10	16,5	6,5	26	2,5	35	22	27	18	M6	M5	-	-	46	19,99 €
WJRM01-16	25	9	34,5	5	48	30	33	27	M8	M6	32	28	131	43,67 €
WJRM01-20	30	9	42,5	6	52	34	38	36	M8	M6	37	37	232	50,98 €


Dimensions in mm

## Altri prodotti...



J51

Riduttore coassiale a treni paralleli, da 0.13 a 0.49 - a treni para...



NK80

Guida mini Drylin® N, Larghezza 80mm




BOX-WM

Rondella semplice - DIN125, Valigetta di rondelle acciaio



YG2

Ingranaggio dritto PRESTAZIONE, Acciaio 35NCD6



M1

Ruota per vite senza fine, Plastica lavorata (delrin)



PRF-SRA

Sistema di chiusura per profili alluminio, Serruta




HCA

Grano magnetico con esagono incassato, Acciaio



BPPEBLU

Sfera portante Agro,



PRF\_PIV

Cerniere e giunti, Fulcro per porta



BTC\_M

Tappo per tubo quadrato con inserto



IBjss

Snodo angolare, Inox



M0

Ruote per vite senza fine, Bronzo

## Prodotti correlati



WS10

Guida modulabile Drylin® W, Binario



WS16

Binario Drylin® W, Binario



WS20

Binario Drylin® W, Binario