


# Linear guide system Drylin® W

## WJRM



## Hybrid bearings

- Drylin W hybrid bearings offer a unique combination of sliding and rolling movement. Depending on the mounting arrangement used, the use of maintenance free rollers reduce the driving force required. Any shear forces or shock forces are absorbed by the bearing. This hybrid bearing is ideally suited for manual adjustments especially in the applications such as door adjustments.
- Low driving force required, coefficient of friction 0.04 to 0.05 $\mu$
- Highly cost effective solution
- Can be used with any of 7 profiles rails such as WS10, WS16 and WS20



### Application

- Adjustable doors, machine guards, simple handling systems, furniture



**New**

# Linear guide system Drylin® W


Sizes 10-16-20

**WJRM**

- **Material :**  
Zamack  
Liner manufactured from iglidur J

**Advantages**

- No lubrication required
- Small size
- Lightweight

**NEW!****DISCOUNTS**

Qty	1+	6+	20+
Disc	Pri. -10%	On request	

Part number	Static load (W)	Dynamic load capacity for a total travel distance of (km)			F <sub>xv</sub> Max (N.m/s)
		10 (N)	100 (N)	200 (N)	
WJRM01-10	250	250	90	50	50
WJRM01-16	400	400	140	70	80
WJRM01-20	550	550	200	100	80

Part number	A1	A3	B	B2	C1	C3	G1	H	K2	K3	Q1	Q2	Weight (g)	Price each 1 to 5
WJRM01-10	16,5	6,5	26	2,5	35	22	27	18	M6	M5	-	-	46	19,99 €
WJRM01-16	25	9	34,5	5	48	30	33	27	M8	M6	32	28	131	43,67 €
WJRM01-20	30	9	42,5	6	52	34	38	36	M8	M6	37	37	232	50,98 €

Dimensions in mm

## Altri prodotti...



PRF\_VTM  
Fissaggio, Vite testa  
martello



ASL  
Anello di  
sollevamento, a 45° a  
saldare



CHAEpac  
Square decorative  
screwed hinges,  
carbon fibre  
reinforced



DOMI50  
Accessori di  
collegamento, Piastra



CHMR63  
Riduttore a ruota e  
vite senza fine, fino a  
196 Nm



SHN  
Dado esagonale -  
DIN934, Acciaio (Class  
6|8)



HTD8M-BAR  
Barra dentata per  
cinghia RPP, HTD8



FHCSS  
Vite a testa svasata  
piana, Inox A2 - DIN  
7991



PRF\_GAL  
Rotella per profilo  
alluminio, Rotella



PRS50  
Piede snodato tutto  
inox Ø50, Ø 50



RFV40  
Riduttore inox a ruota  
e vite senza fine, fino



PM2  
Vite senza fine,  
Acciaio non temprato

## Prodotti correlati



WS10  
Guida modulabile  
Drylin® W, Binario



WS16  
Binario Drylin® W,  
Binario



WS20  
Binario Drylin® W,  
Binario