Spur gear with clamp

Module 0,5

Teeth in polyacetal

- ***Spur gear are attached to the shaft by a friction coupling***
- *Precision grade JIS grade N10 (JIS B1702-1: 1998)*
- *Material:*
  Teeth polyacetal
  Hub Stainless steel 303




Assembly

- *Recommended shaft tolerances: g6, h6 or h7*
- *Torque slippage should be considered when making a selection*

Info

- **Torque(bending strength)*



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØB Boss	ØA Bore	E	L	ØM screw	J	K	Torque* (Nm)	Slipping torque (Nm)	Mass (kg)	Price each
ZG0.5-36/SC	36	18	19	14	5	5	13,5	M2,5	3,3	4,4	0,49	0,62	0,012	
ZG0.5-40/SC	40	20	21	14	5	5	13,5	M2,5	3,3	4,4	0,55	0,62	0,012	
ZG0.5-50/SC	50	25	26	14	5	5	13,5	M2,5	3,3	4,4	0,73	0,62	0,013	
ZG0.5-60/SC	60	30	31	14	5	5	13,5	M2,5	3,3	4,4	0,90	0,62	0,015	
ZG0.5-80/SC	80	40	41	19	8	5	15	M3	4,5	6,0	1,25	2,22	0,019	
ZG0.5-120/SC	120	60	61	19	8	5	15	M3	4,5	6,0	1,93	2,22	0,040	

Dimensions in mm

Altri prodotti...



CHNrb

Catena segnaletica rossa e bianca, Acciaio



BLHB40

Rinvio angolare ad albero cavo, fino a 10.3 Nm



H2

Ingranaggio elicoidale ad assi incrociati a 90°, Acciaio 20NCD2



PFC

Piede fisso, Livellamento per piccoli elementi



BS3

Panamech, Multi-Beam inox, Inox - con vite a pressione



SBF

Sealed flange bearing unit for Food Industry, cover



DOMI120

Slitta di regolazione Domino 120, Slitta DOMILINE 120 con contatore ...



RCX-6

Rondella sferica - DIN6319, convessa



PSG125S

Ingranaggio dritto di precisione, Inox 316



PM3

Ruota per vite senza fine, Bronzo



LVT

Mini martinetto motorizzato 2A, 2 ampere



PRES7HR

Pressa manuale da banco, Pressione fino a 700kg

Prodotti correlati



G0

Ingranaggio dritto acciaio, Acciaio 20NCD2



ZG0

Ingranaggio dritto in plastica, Plastica lavorata (delrin)



SSG0

Ingranaggio dritto Inox, Inox 304L



PSG05

Ingranaggio dritto di precisione, Acciaio 35NCD6 pretrattato