

Spur gear with clamp

Module
1,0

Teeth in polyacetal



- Spur gear are attached to the shaft by a friction coupling
- Precision grade JIS grade N10 (JIS B1702-1: 1998)
- Material:
Teeth polyacetal
Hub Stainless steel 303

Assembly




- Recommended shaft tolerances: g6, h6 or h7
- Torque slippage should be considered when making a selection.

Info

- *Torque(bending strength)

NEW !

with clamping jaws



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØB Boss	ØA Bore	E	L	ØM screw	J	K	Torque* (Nm)	Slipping torque (Nm)	Mass (kg)	Price each
ZG1-20/SC	20	20	22	14	5	6	14,5	M2,5	3,3	4,4	0,96	0,62	0,013	
ZG1-24/SC	24	24	26	14	5	6	14,5	M2,5	3,3	4,4	1,22	0,62	0,014	
ZG1-25/SC	25	25	27	14	5	6	14,5	M2,5	3,3	4,4	1,28	0,62	0,014	
ZG1-30/SC	30	30	32	19	8	6	16	M3	4,5	6,0	1,61	2,22	0,027	
ZG1-32/SC	32	32	34	19	8	6	16	M3	4,5	6,0	1,75	2,22	0,027	
ZG1-36/SC	36	36	38	19	8	6	16	M3	4,5	6,0	2,04	2,22	0,029	
ZG1-40/SC	40	40	42	19	8	6	16	M3	4,5	6,0	2,33	2,22	0,031	
ZG1-50/SC	50	20	52	19	8	6	16	M3	4,5	6,0	3,07	2,22	0,037	
ZG1-60/SC	60	60	62	19	8	6	16	M3	4,5	6,0	3,78	2,22	0,045	
ZG1-80/SC	80	80	82	19	8	6	16	M3	4,5	6,0	5,23	2,22	0,063	
ZG1-100/SC	100	100	102	19	8	6	16	M3	4,5	6,0	6,68	2,22	0,087	

Dimensions in mm

Altri prodotti...



PCS50

Pignone a catena - acciaio, 12.7mm (DIN08B-1)




UFX

Giunto elastico Uneflex®, economica



PSG2

Ingranaggio dritto di precisione, Acciaio 20NCD2 cementato temprato



FRss

Inserti filettati, Inox



BEK

Vite a ricircolo di sfere miniatura, Supporto



RBG

Ruota, Rivestimento in gomma - nucleo in polipropilene



PRF_CLIP_45

Clip di fissaggio per cavi per profili alluminio, Per canalina di ca...



TBD

Tavola di posizionamento a passo inverso manuale, 40kg



BOXINS300

Inserto autofilettante, Box kit per materiali




VBFP

Volantino a 6 lobi - boccia passante,



MSP38

Inserto con piastrina a incollare



BMF

Manopola, Zigrinata - Passante

Prodotti correlati